



# **PHILMAC 3G FITTINGS**

## Self-regulating heating cables options, ELSR-MA-BF models




Philmac 3G ID and CTSOD fittings are specialized fittings, supplied preassembled and ready to use. It is important to correctly identify what type of pipe is being connected.

Identifying the type of pipe is key to ensuring a simple and effective connection. Philmac 3G ID and CTSOD fittings must be used with the right type of pipe to ensure the system works properly. Ouellet Canada is not responsible for incorrect pipe identification.

## We offer fittings for:


## 1. Polyethylene pipes - ID fittings






Tightened nut with a wrench

## 2. Copper Tube Size outside diameter pipes - CTSOD fittings





Tightened nut with a wrench

#### IPEX "Pipe-with-the-Stripe" example









1 1/4" ID





## **PHILMAC 3G FITTINGS**

## Self-regulating heating cables options, ELSR-MA-BF models



### 1. Polyethylene pipes - ID fittings



Philmac 3G ID fittings can be used with IPEX "Pipe-with-the-Stripe" (except Gold/Yellow Stripe) and ID series (inside diameter) polyethylene (PE) pipes.

#### IPEX "Pipe-with-the-Stripe":

- black stripe, Poly blue
- white stripe
- blue stripe
- red stripe1
- green stripe<sup>1</sup>

#### Polyethylene pipes:

- CSA 50<sup>1</sup>
- Irrigation 2000
- · Utility Pipe

## **ID fitting options**

| Product #              | Description   |  |
|------------------------|---|--|
| KIT-OSR-MABF-PH-34-ID  | Quick connect plumbing kit for 3/4" ID polyethylene pipes for MA-BF cable   |  |
| KIT-OSR-MABF-PH-1-ID   | Quick connect plumbing kit for 1"ID polyethylene pipes for MA-BF cable      |  |
| KIT-OSR-MABF-PH-114-ID | Quick connect plumbing kit for 1 1/4" ID polyethylene pipes for MA-BF cable |  |
| KIT-OSR-MABF-PH-112-ID | Quick connect plumbing kit for 1 1/2" ID polyethylene pipes for MA-BF cable |  |

## 2. Copper Tube Size outside diameter pipes – CTSOD fittings

Philmac 3G CTSOD fittings are Philmac 3G fittings that can be used with IPEX Gold/Yellow Stripe pipes and any other polyethylene (PE) pipe with a Copper Tube Size outside diameter pipes (CTSOD).

The table below shows the relationship between common outside diameters of CTS pipes and the Philmac 3G CTSOD fitting size required.

| Outside diameter of CTS pipes            | 1 1/8" à 1 1/3" OD | 1 3/8" à 1 3/5" OD | 1 5/8" à 1 7/8" OD |
|--|--------------------|--------------------|--------------------|
| Diameter of the Philmac 3G CTSOD fitting | 1″                 | 1 1/4"             | 1 1/2"             |

## **CTSOD fitting options**

| Product #                 | Description   |
|---------------------------|---|
| KIT-OSR-MABF-PH-1-CTSOD   | Quick connect plumbing kit for 1" OD polyethylene CTS pipes for MA-BF cable     |
| KIT-OSR-MABF-PH-114-CTSOD | Quick connect plumbing kit for 1 1/4" OD polyethylene CTS pipes for MA-BF cable |
| KIT-OSR-MABF-PH-112-CTSOD | Quick connect plumbing kit for 1 1/2" OD polyethylene CTS pipes for MA-BF cable |



<sup>&</sup>lt;sup>1</sup> These pipes connected to Philmac 3G ID fittings are CSA certified for potable water supply systems.